



15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/200A 12kAIC fuseholder

By Chance
Catalog # [CP710143P](#)

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 200A, 12kAIC fuseholder, parallel-groove connector and no bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

Bracket Type	No Bracket
Catalog Number	CP710143P
Description - Replacement	T710-143T
Fuse Holder	
Type	Cutout
UPC	096359383987

Dimensions

Dimensions	14.500 in x 14.500 in x 4.938 in
Height	4.938 in
Length	14.5 in
Weight	12.211 lb
Width	14.5 in

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)



Current Rating	200 A
Fuselink Current Range	140A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
--------------------------	---

Logistics

Pallet Quantity	63
Standard Package	1

Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - 110KV BIL Polymer Cutout](#)
- [Specifications - CP710143P](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand