



# 15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/200A 12kAIC fuseholder

By Chance  
Catalog # [CP710143PV](#)

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 200A, 12kAIC fuseholder, large eyebolt connector and Easy On NEMA "B" crossarm bracket.



## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings

## General

Bracket Type	Easy On NEMA "B" for crossarm
Catalog Number	CP710143PV
Corrosion Resistant?	No
Description - Replacement	T710-143T
Fuse Holder	
Type	Cutout
UPC	096359668046

## Dimensions

Weight	12 lb
--------	-------

## Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	200 A
Fuselink Current Range	101A to 200A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

## Logistics

Pallet Quantity	63 EA
Standard Package	1

## Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
CH-CP710143PV-SPEC-EN | REV 6/2024