



20/34.5 kV, 150 kV BIL, Type C
Loadbreak Porcelain Cutout /
Arrester Combination w/100A
12kAIC fuseholder

By Chance
Catalog # C73DN313LX



20/33.5 kV, 150 kV BIL, Loadbreak Type C Porcelain Cutout /
Arrester Combination with a 100A, 12kAIC fuseholder, large
eyebolt connector and an extended NEMA "B" crossarm bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	C73DN313LX
Description - Replacement	T730-313T
Fuse Holder Type	Cutout

Electrical Ratings

BIL	150 kV
-----	--------

Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.4kV; *20.8 thru 34.5kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	51.8 micro-volts @ 22kV
Voltage Rating	20/33.5 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- Catalogs - [Type C-Porcelain Cutouts](#)
- Literature - [Switching Line Card_FAQ_2019](#)
- Specifications - [C73DN313LX](#)
- Video - [Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- Video - [Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)