



27 kV, 125 kV BIL, Type C Standard Polymer Cutout w/200A 10kAIC fuseholder

By CHANCE Utility
Catalog # CP710242LB

27 kV, 125 kV BIL, Standard Type C Polymer Cutout with a 200A, 10kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T710-242T |
| Type | Cutout |
| UPC | 096359579953 |

Electrical Ratings

| | |
|-----------------------------------|------------------|
| BIL | 125 kV |
| Creep and Leakage Distance | 17.1" (434mm) |
| Current Rating | 200 A |
| Fuselink Current Range | 140A to 200A |
| Reference Voltage Limit - Minimum | Thru 24.9kV |
| Temperature Rise - Max. at 300A | 33° C |
| Voltage - Maximum | 27 kV |
| Voltage - Radio Interference | Ambient @15.66kV |
| Voltage Rating | 27 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 42 EA |
| Standard Package | 1 |

Product Assets

[Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, 27 KV 125 BIL Polymer \(CP710-2\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-CP710242LB-SPEC-EN | REV 1/2024