



27 kV, 150 kV BIL, Type C Standard Polymer Cutout w/100A 12kAIC fuseholder

By Chance

Catalog # [CP710313EVMS](#)

27 kV, 150 kV BIL, Standard Type C Polymer Cutout with a 100A, 12kAIC fuseholder, small eyebolt connector and Easy On NEMA "B" crossarm bracket, Mechanical assist spring option.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

Bracket Type	Easy On NEMA "B" for crossarm
Catalog Number	CP710313EVMS
Corrosion Resistant?	Yes
Description - Replacement Fuse Holder	T710-313TM
Type	Cutout
UPC	096359655879

Dimensions

Weight	12 lb
--------	-------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	23.6" (600mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV



Logistics

Pallet Quantity	42
Standard Package	1

Product Assets

[Catalogs - Type C-Polymer Cutouts](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, 27 KV 150 BIL Polymer](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP710313EVMS-SPEC-EN | REV 6/2024