




36 kV, 170 kV BIL, Type C Standard Polymer Cutout w/300A Solid Blade

By Chance

Catalog # [CP710633LX](#)

36 kV, 150 kV BIL, Standard Type C Polymer Cutout with a 300A, 12kAIC solid blade, large eyebolt connector, extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

| | |
|---------------------------|--------------------------------|
| Bracket Type | Extended NEMA "B" for crossarm |
| Catalog Number | CP710633LX |
| Corrosion Resistant? | No |
| Description - Replacement | T710-633T |
| Fuse Holder | |
| Type | Cutout |
| UPC | 096359655046 |

Dimensions

| | |
|--------|---------|
| Weight | 12.5 lb |
|--------|---------|

Electrical Ratings

| | |
|-----------------------------------|---------------|
| BIL | 170 kV |
| Creep and Leakage Distance | 33.2" (845mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | Thru 34.5kV |
| Voltage - Maximum | 36 kV |
| Voltage Rating | 36 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 24 EA |
| Standard Package | 1 |

Product Assets

[Catalogs - Type C-Polymer Cutouts](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, 36 KV 170 BIL Polymer](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP710633LX-SPEC-EN | REV 6/2024