



36 kV, 170 kV BIL, Type C Standard Polymer Cutout w/300A Solid Blade

By Chance
Catalog # [CP710633PB](#)

36 kV, 150 kV BIL, Standard Type C Polymer Cutout with a 300A, 12kAIC solid blade, parallel-groove connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	CP710633PB
Corrosion Resistant?	No
Description - Replacement	T710-633T
Fuse Holder	
Type	Cutout
UPC	096359644750

Dimensions

Weight	12.5 lb
--------	---------

Electrical Ratings

BIL	170 kV
Creep and Leakage Distance	33.2" (845mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 34.5kV
Voltage - Maximum	36 kV
Voltage Rating	36 kV

Logistics

Pallet Quantity	24 EA
Standard Package	1

Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Installation Manuals - Standard Cutout Installation Instructions](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Cutout, 36 KV 170 BIL Polymer](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP710633PB-SPEC-EN | REV 6/2024