



15 kV, 110 kV BIL, Type C Standard Polymer Cutout / Arrester Combination w/100A 10kAIC fuseholder

By Chance

Catalog # [CP71DM112PB](#)

15 kV, 110 kV BIL, Standard Type C Polymer Cutout / Arrester Combination with a 100A, 10kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- DG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	CP71DM112PB
Description - Replacement	T710-112T
Fuse Holder	
Type	Cutout
UPC	096359368953

Dimensions

Dimensions	24.500 in x 21.500 in x 6.000 in
Height	6 in
Length	24.5 in
Weight	22.471 lb
Width	21.5 in



Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

[Catalogs - Type C-Polymer Cutouts](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, Arrester 15 KV Polymer](#)
[Specifications - CP71DM112PB](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
CH-CP71DM112PB-SPEC-EN | REV 3/2025