



# 15 kV, 110 kV BIL, Type C Standard Polymer Cutout / Arrester Combination w/100A 16kAIC fuseholder

By Chance  
Catalog # [CP71EL114LBM](#)



15 kV, 110 kV BIL, Standard Type C Polymer Cutout / Arrester Combination with a 100A, 16kAIC fuseholder, large eye-bolt connector and a NEMA "B" crossarm bracket.

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- DG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

## General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	CP71EL114LBM
Description - Replacement	T710-114TM
Fuse Holder Type	Cutout

## Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

## Logistics

Standard Package 1

## Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Cutout, Arrester 15 KV Polymer](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-CP71EL114LBM-SPEC-EN | REV 6/2024