



Fiberglass Crossarm, 25 Deadend, 96" (8'), 2-Wire, 3/4" Bracket, with Dual Sided Eyenuts

By Chance
Catalog # [CDF25G096D2003B](#)



Hubbell Fiberglass Deadend Crossarms are designed to support the conductor when deadending a line or when extra strength is needed, for example, an area with corners or angles or when there are longer spans between poles. Hubbell Fiberglass Crossarms help harden the grid by offering superior fire resistance, longevity, and strength. Hubbell Fiberglass Crossarms are filled with closed cell foam and drilled to your specifications. See part numbering system on drawing for standard drill patterns. We can also accomodate custom drill requests. All Hubbell Fiberglass Crossarms feature a brace-less center mount design with keyhole feature for easy installation. Mounting brackets are made of galvanized steel with 5/8" or 3/4" holes. Deadend brackets include two integrated guy attachments for 7/8" guying hardware. Ultimate guy load is 30K per attachment.

Features

- Sleeves are installed in All drill holes for hardware torque protection Recommended hardware torque: 250 in-lbs.
- Mounting bracket for 3/4" hardware
- Painted gray with UV inhibitor paint
- Drill Pattern 003: RUS Standard 96" Deadend

General

Catalog Number	CDF25G096D2003B
Material	Fiberglass
Strength Rating - Minimum	8,125 lb. lb
Ultimate, Longitudinal (L)	
Type	Arm
UPC	096359833239

Dimensions

Dimensions	96 in x 4-5/8 in x 3.625 in
Height	3.625 in

Length	96 in
Width	4-5/8 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	25
-----------------	----

Product Assets

- [Brochures - Fiberglass Crossarms](#)
- [Catalog Page - FIBERGLASS CONSTRUCTION PRODUCTS](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Interactive Catalog - Fiberglass Construction Products \(12\)](#)
- [Literature - The support you need from the name you trust](#)
- [Literature - Fiberglass Crossarms Technical & Application Questions](#)
- [Sales Drawings - SACDX25](#)
- [Specifications - CDF25G096D2003B](#)



A Hubbell brand