



## 15 kV, 110 kV BIL, Type C Standard Polymer Cutout w/100A 16kAIC fuseholder

By Chance

Catalog # [CP710114PZM](#)

15 kV, 110 kV BIL, Standard Type C Polymer Cutout with a 100A, 16kAIC fuseholder, parallel-groove connector and no bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings

### General

Bracket Type	No Bracket
Catalog Number	CP710114PZM
Description - Replacement	T710-114TM
Fuse Holder	
Type	Cutout
UPC	096359493624

### Dimensions

Dimensions	14.500 in x 14.500 in x 4.938 in
Height	4.938 in
Length	14.5 in
Weight	12.74 lb
Width	14.5 in

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

### Logistics

Pallet Quantity	63 EA
Standard Package	1

### Product Assets

[Catalogs - Type C-Polymer Cutouts](#)  
[Installation Manuals - Standard Cutout Installation Instructions](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)  
[Sales Drawings - 110KV BIL Polymer Cutout](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
CH-CP710114PZM-SPEC-EN | REV 6/2024