



27 kV, 125 kV BIL, Type C Standard Polymer Cutout w/300A Solid Blade

By CHANCE Utility
Catalog # [CP710233EBM](#)

27 kV, 125 kV BIL, Standard Type C Polymer Cutout with a 300A solid blade, small eyebolt connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T710-233TM
Type	Cutout

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	42 EA
Standard Package	1

Product Assets

[Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
[Installation Manuals - Standard Cutout Installation Instructions](#)
[Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, 27 KV 125 BIL Polymer \(CP710-2\)](#)
[Technical Solutions - CH-CP710233EBM-SPEC-EN](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-CP710233EBM-SPEC-EN | REV 1/2024