



## 15 kV, 110 kV BIL, Type C Standard Polymer Cutout / Arrester Combination w/300A Solid Blade

By Chance

Catalog # [CP71FM133PD](#)

15 kV, 110 kV BIL, Standard Type C Polymer Cutout / Arrester Combination with a 300A solid blade, parallel-groove connector and a D-shape pole mounting bracket.



### Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- DG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

### General

Bracket Type	D-shape for pole mounting
Catalog Number	CP71FM133PD
Description - Replacement	T710-133T
Fuse Holder Type	Cutout

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

### Logistics

Standard Package 1

### Product Assets

[Catalogs - Type C-Polymer Cutouts](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Cutout, Arrester 15 KV Polymer](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-CP71FM133PD-SPEC-EN | REV 6/2024