



# 15/27 kV, 125 kV BIL, Type C Linkbreak Polymer Cutout w/100A 12kAIC fuseholder

By CHANCE Utility  
Catalog # [CP720213EB](#)

15/27 kV, 125 kV BIL, Linkbreak Type C Polymer Cutout with a 100A, 12kAIC fuseholder, small eyebolt connector and a NEMA "B" crossarm bracket.



\*Representative Image

## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings

## General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T720-213T
Type	Cutout

## Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	15/27 kV

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Installation Manuals - Link Break Cutout Installation Instructions](#)
- [Literature - SF11036E\\_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Cutout, LKBK 15/27 KV 125 BIL Polymer \(CP720-2\)](#)
- [Technical Solutions - CH-CP720213EB-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.