



15 kV, 110 kV BIL, Type C Linkbreak Polymer Cutout / Arrester Combination w/100A 16kAIC fuseholder

By CHANCE Utility
Catalog # [CP72DM114LD](#)

15 kV, 110 kV BIL, Linkbreak Type C Polymer Cutout / Arrester Combination with a 100A, 16kAIC fuseholder, large eyebolt connector and a D-shape pole mounting bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	D-shape for pole mounting
Description - Replacement Fuse Holder	T720-114T
Type	Cutout

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient
Voltage Rating	15 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout/ Arrester \(SAP72DL1\)](#)
- [Technical Solutions - CH-CP72DM114LD-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-CP72DM114LD-SPEC-EN | REV 1/2024