



15/27 kV, 125 kV BIL, Type C Linkbreak Polymer Cutout / Arrester Combination w/100A 12kAIC fuseholder

By CHANCE Utility
Catalog # CP72EN213LX

15/27 kV, 125 kV BIL, Linkbreak Type C Polymer Cutout / Arrester Combination with a 100A, 12kAIC fuseholder, large eyebolt connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings

General

Bracket Type	Extended NEMA "B" for crossarm
Description - Replacement Fuse Holder	T720-213T
Type	Cutout

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	15/27 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Cutout, Polymer Linkbreak w/Arrester, 27KV, 125KV BIL \(SAP72DN2\)](#)
- [Technical Solutions - CH-CP72EN213LX-SPEC-EN](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-CP72EN213LX-SPEC-EN | REV 1/2024