



15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout w/300A Solid Blade

By CHANCE Utility
Catalog # [CP730133PB](#)

15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout with a 300A solid blade, parallel-groove connector and a NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T730-133T |
| Type | Cutout |
| UPC | 096359407225 |

Dimensions

| | |
|--------|---------|
| Weight | 5.88 lb |
|--------|---------|

Electrical Ratings

| | |
|--|-------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 12.6" (319mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 39° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |
| Withstand Current - Short Time (10 cycles) | 12,000 Amps Asym. |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 24 |
| Standard Package | 1 |

Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Loadbreak 110KV BIL Polymer Cutout \(SAP730-1\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.