




# 15/27 kV, 125 kV BIL, Type C Loadbreak Polymer Cutout w/100A 12kAIC fuseholder

By Chance  
Catalog # [CP730213L](#)

15/27 kV, 125 kV BIL, Loadbreak Type C Polymer Cutout with a 100A, 12kAIC fuseholder, large eyebolt connector and no bracket.



## Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

## General

Bracket Type	No Bracket
Catalog Number	CP730213L
Description - Replacement	T730-213T
Fuse Holder	
Type	Cutout
UPC	096359388234

## Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV

## Logistics

Pallet Quantity	24
Standard Package	1

## Product Assets

[Catalogs - Type C-Polymer Cutouts](#)  
[Installation Manuals - Load Break Cutout Installation Instructions](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)  
[Sales Drawings - Cutout, LDBK 15/27 KV 125 BIL Polymer \(CP730-2\)](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-CP730213L-SPEC-EN | REV 6/2024