



15 kV, 110 kV BIL, Type C Linkbreak Polymer Cutout w/100A 16kAIC fuseholder

By Chance
Catalog # [CP720114L](#)

15 kV, 110 kV BIL, Linkbreak Type C Polymer Cutout with a 100A, 16kAIC fuseholder, large eyebolt connector and no bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Interchangeable with ABB Type ICX & S&C(MPS) Type XS
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings

General

Bracket Type	No Bracket
Catalog Number	CP720114L
Description - Replacement	T720-114T
Fuse Holder	
Type	Cutout

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient
Voltage Rating	15 kV

Logistics

Standard Package 1

Product Assets

[Catalogs - Type C-Polymer Cutouts](#)
[Installation Manuals - Link Break Cutout Installation Instructions](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
[Sales Drawings - Linkbreak 110 KV BIL Polymer Cutout](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP720114L-SPEC-EN | REV 6/2024