



**15/27 kV, 125 kV BIL, Type C
Loadbreak Polymer Cutout
w/300A Solid Blade**

By CHANCE Utility
Catalog # [CP730233LX](#)

15/27 kV, 125 kV BIL, Loadbreak Type C Polymer Cutout with a 300A solid blade, large eyebolt connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 – 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

General

| | |
|---------------------------------------|--------------------------------|
| Bracket Type | Extended NEMA "B" for crossarm |
| Description - Replacement Fuse Holder | T730-233T |
| Type | Cutout |
| UPC | 096359612681 |

Electrical Ratings

| | |
|--|--|
| BIL | 125 kV |
| Creep and Leakage Distance | 17.1" (434mm) |
| Current Rating | 300 A |
| Reference Voltage Limit - Minimum | No Restrictions thru 14.9kV; *20.8 thru 24.9kV |
| Temperature Rise - Max. at 300A | 40° C |
| Voltage - Radio Interference | 36.2 micro-volts @ 15.66kV |
| Voltage Rating | 15/27 kV |
| Withstand Current - Short Time (10 cycles) | 12,000 Amps Asym. |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
[Installation Manuals - Load Break Cutout Installation Instructions](#)
[Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Cutout, LDBK 15/27 KV 125 BIL Polymer \(CP730-2\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.