



15/27 kV, 125 kV BIL, Type C Loadbreak Polymer Cutout w/200A 10kAIC fuseholder

By Chance

Catalog # [CP730242LX](#)

15/27 kV, 125 kV BIL, Loadbreak Type C Polymer Cutout with a 200A, 10kAIC fuseholder, large eyebolt connector and an extended NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	CP730242LX
Description - Replacement	T730-242T
Fuse Holder	
Type	Cutout

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	17.1" (434mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	36.2 micro-volts @ 15.66kV
Voltage Rating	15/27 kV

Logistics

Standard Package 1

Product Assets

[Catalogs - Type C-Polymer Cutouts](#)

[Installation Manuals - Load Break Cutout Installation Instructions](#)

[Literature - Switching Line Card_FAQ_2019](#)

[Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)

[Sales Drawings - Cutout, LDBK 15/27 KV 125 BIL Polymer \(CP730-2\)](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)

[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP730242LX-SPEC-EN | REV 6/2024