




15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout / Arrester Combination w/300A Solid Blade

By Chance
Catalog # [CP73EM133LD](#)

15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout / Arrester Combination with a 300A solid blade, large eyebolt connector and a D-shape pole mounting bracket.



Features

- Fully compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

General

Bracket Type	D-shape for pole mounting
Catalog Number	CP73EM133LD
Description - Replacement	T730-133T
Fuse Holder Type	Cutout

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Standard Package 1

Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - 110KV BIL Polymer Cutout/ Arrester](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality Experience](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)

