



15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout w/100A 10kAIC fuseholder

By CHANCE Utility
Catalog # CP730112LX

15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout with a 100A, 10kAIC fuseholder, large eyebolt connector and an extended NEMA "B" crossarm bracket.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

General

Bracket Type	Extended NEMA "B" for crossarm
Description - Replacement Fuse Holder	T730-112T
Type	Cutout

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Type C-Polymer Cutouts \(10AA\)](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - SF11036E_HPS CHANCE RUS Cutout Listing](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Loadbreak 110KV BIL Polymer Cutout \(SAP730-1\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience \(VI10004E\)](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality \(VI10005E\)](#)



A proud member of the Hubbell Family.