



15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout w/100A 16kAIC fuseholder

By Chance
Catalog # [CP730114EB](#)

15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout with a 100A, 16kAIC fuseholder, small eyebolt connector and a NEMA "B" crossarm bracket.



Features

- Fully Compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP (Enhanced Silicone Polymer) Insulating Material
- TDG (Thermal Diffusion Galvanization) Insulator Assembly Castings
- Non Interchangeable Mounting Assembly

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Catalog Number	CP730114EB
Description - Replacement	T730-114T
Fuse Holder	
Type	Cutout
UPC	096359565147

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

- [Catalogs - Type C-Polymer Cutouts](#)
- [Installation Manuals - Load Break Cutout Installation Instructions](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Literature - HUBBELL® | CHANCE® RUS CUTOUT LISTING](#)
- [Sales Drawings - Loadbreak 110KV BIL Polymer Cutout](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)
- [Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-CP730114EB-SPEC-EN | REV 6/2024