




# 15 kV, 110 kV BIL, Type C Loadbreak Polymer Cutout / Arrester Combination w/100A 10kAIC fuseholder

By Chance  
Catalog # [CP73DM112EX](#)



15 kV, 110 kV BIL, Loadbreak Type C Polymer Cutout / Arrester Combination with a 100A, 10kAIC fuseholder, small eyebolt connector and an extended NEMA "B" crossarm bracket.

## Features

- Fully compliant with ANSI/IEEE C37.41 & C37.42 - 2016
- Single Vent Solid Cap Design
- Uses Universal Style Fuse Links
- Synthetic Arc Quenching Fuse Holder Liner Material
- ESP ( Enhanced Silicone Polymer ) Insulating Material
- TDG ( Thermal Diffusion Galvanization ) Insulator Assembly Castings
- Ohio Brass Distribution Class Arresters in Standard, Heavy and Riser Pole Duty Ratings
- Non Interchangeable Mounting Assembly

## General

Bracket Type	Extended NEMA "B" for crossarm
Catalog Number	CP73DM112EX
Description - Replacement Fuse Holder	T730-112T
Type	Cutout

## Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

## Logistics

Standard Package 1

## Product Assets

[Catalogs - Type C-Polymer Cutouts](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - 110KV BIL Polymer Cutout/ Arrester](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 3: Quality](#)  
[Video - Hubbell Power Systems Cutout Seminar, Part 2: Experience](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
CH-CP73DM112EX-SPEC-EN | REV 6/2024