



# LEAD, RS3500.300, 10/12/14 X 10ft

By Chance  
Catalog # [CRSLCBCDF10](#)

Round Shaft Lead Section 10' long 3.5" Diameter 10" - 12" - 14" Helices.



### Features

- Round Shaft Lead Sections are assembled to Round Shaft Extension with through bolt(s).
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of pile can be determined my measuring installation torque

### Application

Helical Anchoring

### General

Catalog Number	CRSLCBCDF10
Coating	Galvanized, ASTM A-153
Number of Helices	3
Pipe Type	Round Pipe
Shaft Type	RS
Style	Round Shaft Helical Piles RS3500.300
Torque Rating	13000 ft-lbs
Type	Lead Sections

### Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in
Foundation Diameter	3.5 in
Foundation Length	120 in
Length	120 in

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Case Studies - NE Power Coop Sub Foundations](#)
- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Helical Piles Installation Instructions](#)
- [Installation Manuals - Type RS3500.300 Helical Pile Building Code](#)
- [Installation Manuals - Type RS3500.300 Helical Pile](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Transmission & Substation Design Request Form](#)
- [Literature - Helical Foundation GA Coast](#)
- [Sales Drawings - Leads And Extensions](#)
- [Specifications - CRSLCBCDF10](#)
- [Video - CHANCE Round Shaft Anchor Installation](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)