



LONG SHANK LINE POST STUD, 5/8in x 10in

By Chance
Catalog # [DF19M19](#)

Line post stud screws into metal base of post insulators for pole installations.

Features

- 3/4"-10UNC insulator thread x 15/16" long
- Serrated flange
- Hex collar
- 10" long shank has 4" thread length
- Includes one single-coil lock washer, one 3" square curved washer, square nut and MF lock nut
- Gavanized steel per ASTM A-153

General

Catalog Number	DF19M19
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Line Post Stud
UPC	096359369530



Dimensions

Dimensions	11.250 in x 3.000 in x 3.000 in
Distance From Pole	N/A
Height	3 in
Length	11.25 in
Length - Threaded Area	4
Weight	1.74 lb
Width	3 in

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

- [Catalogs - Pole Line Hardware Supplements](#)
- [Sales Drawings - Line Post Stud](#)
- [Specifications - DF19M19](#)



A Hubbell brand