



LONG SHANK LINE POST STUD, 5/8in x 10in

By CHANCE Utility
Catalog # [DF19M20](#)

Line post stud screws into metal base of post insulators for pole installations.



*Representative Image

Features

- 3/4"-10UNC insulator thread x 15/16" long
- Serrated flange
- Hex collar
- 10" long shank has 4" thread length
- Includes one single-coil lock washer, one 3" square curved washer, square nut and MF lock nut
- Galvanized steel per ASTM A-153

General

Coating	Galvanized, ASTM A-153
Material	Steel
Type	Line Post Stud
UPC	096359369547

Dimensions

Distance From Pole	N/A
Length	12.00 in
Length - Threaded Area	4
Weight	1.87 lb

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

[Catalogs - Pole Line Hardware Supplements \(5-53Supp1-19\)](#)
[Sales Drawings - Line Post Stud \(SADF19M20\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-DF19M20-SPEC-EN | REV 7/2023