



LONG SHANK LINE POST STUD, 3/4in x 24in

By Chance
Catalog # [DF19M32](#)

Line post stud screws into metal base of post insulators for pole installations.

Features

- 3/4"-10UNC insulator thread x 15/16" long
- Serrated flange
- Hex collar
- 24" long shank has 4" thread length
- Includes one single-coil lock washer, one double coil lock washer, one 2-1/4" square washer, square nut and MF lock nut
- Gavanized steel per ASTM A-153

General

Catalog Number	DF19M32
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Type	Line Post Stud
UPC	096359485537



Dimensions

Distance From Pole	N/A
Length	24 in
Length - Threaded Area	4
Weight	3.35 lb

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

[Sales Drawings - Stud Line Post](#)
[Specifications - DF19M32](#)



A Hubbell brand