



# 24" 16K Guy Strain, Clevis / Clevis + 2 Rollers

By Chance  
Catalog # [GS16024CC2](#)

24" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Clevis + 2 Rollers

## Features

- 5/8" diameter fiberglass rod
- End fittings are hot dip galvanized ductile iron

## General

Catalog Number	GS16024CC2
Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb.
UPC	096359036968

## Dimensions

Diameter - Rod / Tube	0.625 in
Dimensions	24 in x 0.66 in x 0.5 in
Height	0.5 in
Length	24 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in



\*Representative Image

Mounting Bolt Spacing	32 in
Weight	3.68 lb
Width	0.66 in

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
--------------------------	---

## Logistics

Standard Package	10
------------------	----

## Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - Guy Strain, 16 K Clevis, 1 Roller](#)
- [Specifications - GS16024CC2](#)



A Hubbell brand