



## Spiral Link Stick, 31"

By: CHANCE Lineman Tools & Equipment  
Catalog # [H4722](#)



The 31" Spiral Link Stick is used in lieu of a strain link stick in close places where the lineman cannot safely install a strain link stick by hand. A lifting eye on the head ferrule enables the lineman to guide the Spiral Link Stick to the conductor with a hotstick. The pole of the Spiral Link Stick is made of 1-1/4" Epoxiglas™. Ferrule castings are of heat-treated aluminum alloy; spiral hook and butt ring of galvanized steel.

\*Representative Image

### Features

- Tested per OSHA & ASTM F711
- Replaces strain link stick when lineman cannot safely install one by hand
- A lifting eye on the head ferrule enables the lineman to guide the Spiral Link Stick to the conductor with a hotstick
- 1-1/4" Epoxiglas™ pole
- Heat-treated aluminum alloy ferrule castings
- Galvanized-steel spiral hook and butt ring

### General

Max Load Lbs.	3500 lb
Style	Spiral Link Stick
UPC	096359040835

### Dimensions

Dimensions	34.5 in x 7.25 in x 7.25 in
Height	7.25 in
Length	34.5 in
Length - Insulated Section	15.5 in
LengthMetric	87.6 mm
Weight	7 lb
WeightMetric	3.2 kg
Width	7.25 in

### Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Wire Size	1510.5 kcmil ACSR

### Logistics

Pallet Quantity	32
-----------------	----

### Product Assets

- [Catalogs - Transmission Tools \(2250\)](#)
- [Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>
- [Literature - Transmission Project Tools and Equipment Checklist \(CENT\\_LTE\\_FRM\\_EN\\_00082\)](#)
- [Sales Drawings - SA\\_H4722\\_A](#)



A proud member of the Hubbell Family.