




# 1.6 A, Type Slo-Fast Fuselinks, 26" Length, Solid Head

By Chance  
Catalog # M1D6SF

1.6 amp, Type SloFast Cutout fuselink with a 26" (660.4mm) pigtail.



### Features

- Comparable to Cooper/Kearney Type X fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design specific for transformer protection
- Slow portion of time current characteristic curve closely matches transformers safe loading curve
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Catalog Number	M1D6SF
Fuse Head Style	Solid
Fuselink Type	Type SloFast
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359616580

### Dimensions

Length - Fuselink 26" (660.4mm)

### Electrical Ratings

Amperage Rating 1.6 A

### Logistics

Carton Quantity 10  
 Pallet Quantity 4800  
 Standard Package 1

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type SloFast](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type SloFast](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type SF Solid & Removable HD](#)
- [Specifications - M1D6SF](#)
- [Test Documents - SloFast Total Clear](#)
- [Test Documents - SloFast Min Melt](#)