



# 27 kV, 125 kV BIL, 600 A, Porcelain (2 1/4" Bolt Circle) insulation, M3 Switch

By CHANCE Utility  
Catalog # M3D63ACL

25 kV, 125kV, 600 A, Single-Phase Hookstick Disconnect Switch.



\*Representative Image

## Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 & 38kV Voltage Classes
- 110, 125, 150, 200kV BIL Insulation Levels
- 600A & 900A Current Ratings
- Porcelain and ESP Polymer Insulator Assemblies with 2.25" Bolt Circles
- Distribution Base, Serrated Slots
- Load Break Option Available

## General

Base Type	Distribution Base, Serrated Slots
Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	1,000 Lbs (4.45kN)
Color - Insulator	Sky Gray
Contact	Silver
Description - Captive Hardware	Consist of 4 each: 1/2" 13 Stainless Steel Splined Bolt, 1/2" Lockwasher and Bronze Nut
Insulator Type	Porcelain (2 1/4" Bolt Circle)
Material - Base	Galvanized Steel per ASTM A153
Tension Range	5000 lb
Torsional Strength	3,000 in Lbs (339 N-M)
UPC	096359733034

## Dimensions

Bolt Length	10.00 in
Weight	30.38 lb

## Electrical Ratings

Arc Distance - Dry	8.1" (205.7mm)
BIL	125 kV
Creep and Leakage Distance	15.5" (394mm)
Current Overload - 8hr Emergency	1080 A
Current Rating	600 A
Dead-Ending Rating - Working Load	8,000 Lbs
Reference Voltage Limit - Minimum	25 kV
Temperature Rise - Max. at 600A	27°C
Voltage - Maximum	27 kV
Withstand Current - Short Time (10 cycles)	40kA, asymmetrical
Withstand Current - Short Time (2 sec)	25kA, symmetrical
Withstand Current - Short Time (3 sec)	16kA, symmetrical

## Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

## Logistics

Pallet Quantity	20
Standard Package	1

## Product Assets

- [Catalogs - Hookstick Operated Switches \(CA10230E\\_14B\)](#)
- [Installation Manuals - Instructions for CHANCE Type M3 Distribution Switch \(P807-0198\)](#)
- [Installation Manuals - Type M3C Single Insulator Disconnect Switch for Distribution Switching \(PSP8070357\)](#)
- [Installation Manuals - M3\\_Instructions](#)
- [Literature - SA-M3D\\_C](#)
- [Sales Drawings - Type M3 Switch \(SA-M3D\)](#)



A proud member of the Hubbell Family.

