



LONG SHANK LINE POST STUD, 5/8in x 7-1/2in

By Chance
Catalog # [DF19M11](#)

Line post stud screws into metal base of post insulators for crossarm installations.

Features

- 3/4"-10UNC insulator thread x 1-1/16" long
- Serrated flange
- Hex collar
- 7-1/2" long shank has 4" thread length
- Includes two single-coil lock washers,two 2" round washers, one 2" square washer and two square nuts
- Gavanized steel per ASTM A-153

General

Catalog Number	DF19M11
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Type	Line Post Stud
UPC	096359462248



Dimensions

Distance From Pole	N/A
Length	7.5 in
Length - Threaded Area	4
Weight	1.08 lb

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

[Sales Drawings - Stud Line Post](#)
[Specifications - DF19M11](#)



A Hubbell brand