



LONG SHANK LINE POST STUD, 5/8in x 7in

By CHANCE Utility
Catalog # [DF19M2](#)

Line post stud screws into metal base of post insulators for crossarm installations.



Features

- 3/4"-10UNC insulator thread x 1-1/8" long
- Serrated flange
- Hex collar
- 7" long shank has 4" thread length
- Includes one single-coil lock washer, one 2" square washer, square nut and MF lock nut
- Galvanized steel per ASTM A-153

General

Coating	Galvanized, ASTM A-153
Material	Steel
Type	Line Post Stud
UPC	096359365389

Dimensions

Distance From Pole	N/A
Length	7.00 in
Length - Threaded Area	4
Weight	1.02 lb

Logistics

Pallet Quantity	1800
-----------------	------

Product Assets

[Catalogs - Pole Line Hardware Supplements \(5-53Supp1-19\)](#)
[Sales Drawings - Line Post Studs \(SADF19M4\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-DF19M2-SPEC-EN | REV 4/2023