



Duckbill Ground Clamp, Type I- Class A-Grade 5, 1.162" Jaw Opening

By CHANCE Utility
Catalog # [G36221](#)



Duckbill Ground Clamp, Type I-Class A-Grade 5, 1.162" Jaw
Opening

Features

- Duckbill Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 566kcmil CU or 900kcmil ACSR (1.162")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 5
- IEC Rating 35kA (15 cycles)
- Jaws Smooth
- Ferrule Plain-Plug

General

Eye Screw/T-Handle Installation Torque (in-lb)	250 in-lb
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038245

Dimensions

Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Weight	1.47 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	600
-----------------	-----

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-G36221-SPEC-EN | REV 7/2023