



38 kV, 150 kV BIL, 600 A, Polymer (2 1/4" Bolt Circle) insulation, M3 Switch

By CHANCE Utility
Catalog # [M3H68ACL](#)

34.5kV, 150kV, 600 A, Single-Phase Hookstick Disconnect Switch.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 & 38kV Voltage Classes
- 110, 125, 150, 200kV BIL Insulation Levels
- 600A & 900A Current Ratings
- Porcelain and ESP Polymer Insulator Assemblies with 2.25" Bolt Circles
- Distribution Base, Serrated Slots

General

Base Type	Distribution Base, Smooth Slots
Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	800 Lbs (3.56 kN)
Color - Insulator	Dark Gray
Contact	Silver
Description - Captive Hardware	Consist of 4 each: 1/2" 13 Stainless Steel Splined Bolt, 1/2" Lockwasher and Bronze Nut
Insulator Type	Polymer (2 1/4" Bolt Circle)
Material - Base	Galvanized Steel per ASTM A153
Tension Range	5000 lb
Torsional Strength	3,000 in Lbs (339 N-M)
UPC	096359568827

Dimensions

Bolt Length	10.00 in
-------------	----------

Electrical Ratings

Arc Distance - Dry	10" (254mm)
BIL	150 kV
Creep and Leakage Distance	28.2" (716.3mm)
Current Overload - 8hr Emergency	1080 A
Current Rating	600 A
Dead-Ending Rating - Working Load	8,000 Lbs
Reference Voltage Limit - Minimum	34.5kV
Temperature Rise - Max. at 600A	28°C
Voltage - Maximum	38 kV
Withstand Current - Short Time (10 cycles)	40kA, asymmetrical
Withstand Current - Short Time (2 sec)	25kA, symmetrical
Withstand Current - Short Time (3 sec)	16kA, symmetrical

Certifications and Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

- [Catalogs - Hookstick Operated Switches \(CA10230E_14B\)](#)
- [Installation Manuals - M3_Instructions](#)
- [Literature - SA-M3D_C](#)
- [Sales Drawings - Type M3 Switch \(SA-M3D\)](#)



A proud member of the Hubbell Family.

