



Rigid Splice For 1-1/4" Pole

By CHANCE Utility
Catalog # [H33651](#)

RIGID SPLICE KIT FOR 1.25IN POLE, Chance Rigid Pole Splices are recommended for all load conditions-tensile, compressive, or deflection. These Splices make a rigid connection that is stronger than the pole. Use of heat-treated aluminum alloy for the ferrule makes these splices lightweight and keeps spliced poles well balanced. Counter-threaded stainless steel collar locks threaded poles together. The Rigid Splice is available for assembly on Epoxiglas blank poles (above), to shorten Epoxiglas tools for storage or to couple with other spliced tools.



*Representative Image

Features

- Recommended for all load conditions-tensile, compressive, or deflection
- Make a rigid connection that is stronger than the pole
- Use of heat-treated aluminum alloy for the ferrule makes splices lightweight
- Also keeps spliced poles well balanced
- Counter-threaded stainless steel collar locks threaded poles together
- Available for assembly on Epoxiglas blank poles
- Shortens Epoxiglas tools for storage or to couple with spliced tools

General

EU RoHS Indicator	No
Style	Rigid Pole Splices
UPC	096359040194

Dimensions

Weight	0.245 lb
--------	----------

Logistics

Carton Quantity	5
Pallet Quantity	480

Product Assets

[Catalogs - Tools Repair & Storage \(2500\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-H33651-SPEC-EN | REV 8/2023