



27 kV, 150 kV BIL, 900 A, Porcelain (3" Bolt Circle) insulation, M3 Switch

By Chance
Catalog # [M3S94CR](#)



25kV, 150kV LIW, 900 A, Single-Phase Hookstick Disconnect Switch.

Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15 & 27kV Voltage Classes
- 110 and 150kV BIL Insulation Levels
- 600A & 900A Current Ratings
- TR Rated Porcelain and Polymer Insulator Assemblies with 3" Bolt Circles
- Station Base for Structure Mounting

General

Blade Type	Solid Copper (two blade truss-member)
Cantilever Bending Strength - Routine	2,000 Lbs (8.9 kN)
Catalog Number	M3S94CR
Color - Insulator	Sky Gray
Contact	Silver
Description - Captive Hardware	Consist of 4 each: 1/2" 13 Stainless Steel Splined Bolt, 1/2" Lockwasher and Bronze Nut
Insulator Type	Porcelain (3" Bolt Circle)
Material - Base	Galvanized Steel per ASTM A153
Tension Range	10000 lb
Torsional Strength	8,000 in Lbs (903 N-M)

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	24" (609.6mm)
Current Overload - 8hr	1080 A
Emergency	
Current Rating	900 A
Dead-Ending Rating - Working Load	8,000 Lbs
Temperature Rise - Max. at 600A	30°C
Voltage - Maximum	27 kV
Withstand Current - Short Time (10 cycles)	40kA, asymmetrical
Withstand Current - Short Time (2 sec)	25kA, symmetrical
Withstand Current - Short Time (3 sec)	16kA, symmetrical

Certifications And Compliance

Industry Standard(s)	All Applicable ANSI/IEEE Standards
----------------------	------------------------------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Hookstick Operated Switches](#)
- [Sales Drawings - Type M3 Switch](#)
- [Specifications - M3S94CR](#)



A Hubbell brand