



# BOLT, MACHINE, SQ HEAD, 5/8in x 26in, 13,500lbs RATED TENSILE STRENGTH



By Chance  
Catalog # [PS8826CW](#)

Square head machine bolt for utility pole and crossarm construction. Rated for 13,500 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per CSA G-164-M
- Manufactured in compliance with Canadian CSA C83-96 specification
- Charpy level 1 impact - Avg. min. energy absorption of 20J, when tested at -20° C per ASTM A370

### General

Catalog Number	PS8826CW
Coating	Galvanized, CSA G164-M
EU RoHS Indicator	No
Material	Steel
Tensile Strength	14100 lb.
Type	Machine Bolts
UPC	096359404248

### Dimensions

Diameter	0.63 in
----------	---------

Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	26 in
Length - Threaded Area	6 in
Weight	2 lb

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	CSA C83. 23

### Logistics

Carton Quantity	15
Pallet Quantity	840

### Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)  
[Sales Drawings - Bolt, Machine, 5/8" \(Cold Weather CSA\)](#)  
[Specifications - PS8826CW](#)



A Hubbell brand