



BOLT, MACHINE, SQ HEAD, 3/4in x 2in, 20,050lbs RATED TENSILE STRENGTH

By Chance
Catalog # [PS8902CW](#)

Square head machine bolt for utility pole and crossarm construction. Includes one assembled square nut, cone point and 1-3/8" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per CSA G-164-M
- Manufactured in compliance with Canadian CSA C83-96 specification
- Charpy level 1 impact - Avg. min. energy absorption of 20J, when tested at -20° C per ASTM A370

General

Catalog Number	PS8902CW
Coating	Galvanized, CSA G164-M
EU RoHS Indicator	No
Material	Steel
Tensile Strength	22000 lb.
Type	Machine Bolts
UPC	096359404125

Dimensions



*Representative Image

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	2 in
Length - Threaded Area	1.38
Weight	0.53 lb

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Industry Standard(s)	CSA C83. 23

Logistics

Carton Quantity	50
Pallet Quantity	4000

Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)
[Sales Drawings - Bolts, Machine \(Cold Weather CSA\)](#)