



2 Ton Regular Handle Nylon-Strap Ratchet Hoist

By CHANCE Utility
Catalog # [PSC3120000](#)

Every CHANCE Chain Hoist is proof-tested and factory-operated at 150% of capacity rating



Features

- Always use with insulated link sticks of appropriate length
- Plastisol cap on handle end for rubber glove work
- Hotstick rings on hooks and latches
- 2-Ton units employ a sheave-mounted hook in a double-strap becket
- 3'9" Standard lift distance
- 27" minimum between hooks

General

EU RoHS Indicator	No
Strength Rating - Ultimate	4000 lb
Style	Regular Handle
UPC	096359395683
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

Dimensions

Dimensions	22 in x 8.38 in x 5 in
Height	5 in
Length	22 in
LengthMetric	55.9 mm
Weight	20.4 lb
WeightMetric	1814.4 kg
Width	8.38 in

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)
[Installation Manuals - Strap Hoist Instruction Manual \(TD09176E 2\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSC3120000-SPEC-EN | REV 7/2023