



# Barry D.E.W. Line® Tag Line, 40 ft/12.1 m

By Chance  
Catalog # [PSCDEWNK10040](#)

Dielectric Even Wet insulating rope tool designed for performing live line work on AC or DC systems.

## Features

- Rated Working Load 200 lb./90.7 kg
- Meets or exceeds dry or wet electrical requirements of IEC 62196:2009 and ASTM F1701-12
- Cleanable and easy to maintain and test
- Arc-Flash Category 4 rated
- Fixed length with stainless steel thimbles and sealed terminations
- Storage bag with dessicant included

## General

Catalog Number	PSCDEWNK10040
UPC	096359754183
Working Load Limit	200 lb
Working Load Limit Metric	90 kg



\*Representative Image

## Dimensions

Diameter	0.25 in
Diameter - Metric	6 mm
Length	40 ft
Length Metric	12.1 m
Weight	2 lb
WeightMetric	1.8 kg

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Brochures - Barry D.E.W. Line® Insulating Rope Tools](#)  
[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)  
[Specifications - PSCDEWNK10040](#)



A Hubbell brand