



# Barry D.E.W. Line® Work Rope, 100 ft/30.4 m

By Chance  
Catalog # [PSCDEWNP28100](#)

Dielectric Even Wet insulating rope tool designed for performing live line work on AC or DC systems.

## Features

- Rated Working Load 1,260 lb./571.5 kg
- Meets or exceeds dry or wet electrical requirements of IEC 62196:2009 and ASTM F1701-12
- Cleanable and easy to maintain and test
- Arc-Flash Category 4 rated
- Fixed length with stainless steel thimbles and sealed terminations
- Storage bag with dessicant included

## General

Catalog Number	PSCDEWNP28100
Tensile Strength	6,300 lb./2,857 kg
UPC	096359757368
Working Load Limit	1,260 lb



\*Representative Image

Working Load Limit Metric      571 kg

## Dimensions

Diameter	0.5 in
Diameter - Metric	13 mm
Length	100 ft
Length Metric	30.4 m
Weight	12.2 lb
WeightMetric	5.5 kg

## Product Assets

[Brochures - Barry D.E.W. Line® Insulating Rope Tools](#)  
[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)  
[Specifications - PSCDEWNP28100](#)



A Hubbell brand