

Hook, Assembly

By: CHANCE Lineman Tools & Equipment
Catalog # [M47241](#)



The adjustable Hook Assembly can be used with the adjustable strain poles as a direct method of relieving the load on a suspension string. The conductor clamp has a contoured seat with a trapping gripper and is operated by an eyescrew. Conductor range is 1.125" to 25" diameter. The hook can be positioned every 6" on the strain pole. The hook is self-aligning within a range of 45° either side of vertical. The maximum load is 3,500 pounds.

Features

- Snatch blocks hooked into butt ring to keep heandlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4" x 1-3/4" up to 6" x 6"
- Maximum load for the gin is 500 lbs.

General

Style Adjustable Hook Assembly
UPC 096359048022

Dimensions

Dimensions	14 in x 9.5 in x 6 in
Height	6 in
Length	14 in
LengthMetric	35.56 mm
Weight	6 lb
WeightMetric	2.7215542200000002 kg
Width	9.5 in

Logistics

Pallet Quantity 100

Product Assets

[Catalogs - Transmission Tools \(2250\)](#)
[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)