



Barry D.E.W. Line® Work Rope, 150 ft/45.7 m

By Chance
Catalog # [PSCDEWNP28150](#)

Dielectric Even Wet insulating rope tool designed for performing live line work on AC or DC systems.

Features

- Rated Working Load 1,260 lb./571.5 kg
- Meets or exceeds dry or wet electrical requirements of IEC 62196:2009 and ASTM F1701-12
- Cleanable and easy to maintain and test
- Arc-Flash Category 4 rated
- Fixed length with stainless steel thimbles and sealed terminations
- Storage bag with dessicant included

General

| | |
|--------------------|--------------------|
| Catalog Number | PSCDEWNP28150 |
| Tensile Strength | 6,300 lb./2,857 kg |
| UPC | 096359754213 |
| Working Load Limit | 1,260 lb |



*Representative Image

| | |
|---------------------------|--------|
| Working Load Limit Metric | 571 kg |
|---------------------------|--------|

Dimensions

| | |
|-------------------|---------|
| Diameter | 0.5 in |
| Diameter - Metric | 13 mm |
| Length | 150 ft |
| Length Metric | 45.7 m |
| Weight | 17.3 lb |
| WeightMetric | 7.8 kg |

Product Assets

[Brochures - Barry D.E.W. Line® Insulating Rope Tools](#)
[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)
[Specifications - PSCDEWNP28150](#)



A Hubbell brand