



BOLT, OVALEYE, 5/8in x 12in

By Chance

Catalog # [PS29962CW](#)

Ovaleye bolts are used to support suspension insulators in deadend applications.



Features

- 6" thread length and cone point
- Includes one square nut
- Rated tensile strength is 14,100 lbs.
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370
- Galvanized steel per CSAG164-M

General

Catalog Number	PS29962CW
Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	14100 lb.
UPC	096359573524

Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	15.250 in x 2.500 in x 1.000 in
Distance From Pole	N/A
Height	1 in
Length	15.25 in
Length - Threaded Area	6 in
Weight	1.492 lb
Width	2.5 in

Certifications And Compliance

Industry Standard(s)	CSA C83.65
----------------------	------------

Logistics

Carton Quantity	25
Pallet Quantity	1500

Product Assets

- [Catalogs - Fasteners - Canadian Standard \(CSA\)](#)
- [Sales Drawings - 5/8" & 3/4" Ovaleye Bolt \(Cold Weather\)](#)



A Hubbell brand