



TWO-BOLT STATIC WIRE BRACKET, with 5/8in DIA. LINK, 14in LENGTH

By Chance
Catalog # [PS543358](#)

Bracket used with suspension clamp (ordered sperately) to support static wires. Load plate is welded to the rods, while the back plate can be adjusted to fit the pole.

Features

- Designed for 10" to 12" dia. poles
- Bolt diameter is 5/8"
- Furnished with two square and two MF lock nuts
- Plates are curved for installation on round poles
- Galvanized steel per ASTM A-153

General

Catalog Number	PS543358
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Type	Supports
UPC	096359481560

Dimensions

Dimensions	18.000 in x 7.000 in x 2.500 in
------------	---------------------------------



Distance From Pole	N/A
Height	2.5 in
Length	18 in
Length - Threaded Area	6 in
Weight	6.67 lb
Width	7 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	5
Pallet Quantity	120

Product Assets

- [Catalogs - Brackets, Shield Wire Support \(5-53-33\)](#)
- [Sales Drawings - Brackets, Shield Wire Support](#)
- [Specifications - PS543358](#)



A Hubbell brand