



Ground Clamp, C-Type, Type I- Class A-Grade 5, 2.0" Jaw Opening

By CHANCE Utility
Catalog # [T6003203](#)

Ground Clamp, C-Type, Type I-Class A-Grade 5, 2.0" Jaw
Opening



Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 5
- Jaws Smooth
- Threaded Ferrule

General

EU RoHS Indicator	No
Material	Aluminum
Thread Size	5/8-11 UNC
Torque Rating	250 in-lbs
UPC	096359453338

Dimensions

Weight 2.2 lb

Logistics

Pallet Quantity 40

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)

[Sales Drawings - SA_T6003203_GROUND_CLAMP-C-TYPE-I-A-5-_2IN](#)

[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-T6003203-SPEC-EN | REV 8/2023