



## BOLT, MACHINE, SQ HEAD, 1/2in x 1-1/2in, 8,500lbs RATED TENSILE STRENGTH

By Chance  
Catalog # [PS870112CW](#)

Square head machine bolt for utility pole and crossarm construction. Rated for 8,500 lbs. tensile strength. Includes one assembled square nut, cone point and 1-1/2" thread length. Common industry slang reference is crossarm bolt or through bolt.

### Features

- Hot dip galvanized finish per CSA G-164-M
- Manufactured in compliance with Canadian CSA C83-96 specification
- Charpy level 1 impact - Avg. min. energy absorption of 20J, when tested at -20° C per ASTM A370

### General

Catalog Number	PS870112CW
Coating	Galvanized, CSA G164-M
EU RoHS Indicator	No
Material	Steel
Tensile Strength	7575 lb.
Type	Machine Bolts
UPC	096359404071

### Dimensions



\*Representative Image

Diameter	0.5 in
Diameter (Fraction)	1/2 in
Distance From Pole	N/A
Length	1.5 in
Length - Threaded Area	1.5
Weight	0.16 lb

### Certifications And Compliance

Buy American Compliant Industry Standard(s)	Contact Manufacturer CSA C83. 23
---	----------------------------------

### Logistics

Carton Quantity	50
Pallet Quantity	14400

### Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)  
[Sales Drawings - Bolt, Machine, 1/2" \(Cold Weather CSA\)](#)